




Genomflödesarmatur Nitratax clear sc, 5 mm

Produktnr: LZX866

SEK Pris: Kontakta oss

Skickas inom 1 vecka

The through-flow variant is used wherever direct measurement in the medium is not possible for construction related reasons or the medium load makes it necessary to measure a filtered sample.

Specifikationer

Dimension (H x B x D):	210 mm x 500 mm x 160 mm
Fuktade material:	Measuring cell: PVC;
	Seals: EPDM;
	Glands: PVDF;
	Sample tube: PVC
Material:	Measuring cell: PVC;
	Glands: PVDF;
	Sample tube: PVC;
	Screws: Stainless Steel;
	Seals: EPDM
Omgivningstemperatur:	2 - 40 °C (sample temperature)
Provintag:	Tube ID 4 mm/AD 6 mm
Provolym:	0,5 - 10 L
Tryckområde:	Not pressurized, open drain
Vikt :	3,6 kg