



Digital 2-EL konduktivitetssensor, K=0.1 cm-1

Produktnr: D3411.99
SEK Pris: Kontakta oss
Skickas inom 1 vecka

Contacting conductivity sensor for pure medium: 3400 sc family

Analogue 2-electrode sensor for conductivity measurement, with digital gateway for SC controller; with 5m cable between sensor and gateway and 1m cable to controller, flow-through probe incl Pt1000 temperature sensor

Large measuring range

High precision

Wide application range

Stainless steel design

Versatile mounting styles

Specifikationer

Cellkonstant k:	0.1 cm ⁻¹
Garanti :	24 månader
Kabelanslutning :	IP 65 glasfiberförstärkt polyester anslutning
Kärskonstant:	1.00 om den är monterad i 8318 flödeskammare
Längd:	119.5 mm
Mätområde:	0,1 - 200 µS/cm
Mätprincip:	2-EL kontakt konduktivitet
Omgivningstemperatur:	125 °C maximum
Processanslutning:	0.75 " NPT gänga
Specialkommentarer:	Består av: 2-EL ledningsförmåge sensor (Z08311 = A = 0000) 5 m analog kabel (Z08319 = A = 1115) AD gateway (6120700) 1 m digital kabel (6122400) Temperaturgivare: Pt1000

Tryckområde:	Max. 10 bar
Vad ingår i leveransen:	Includes: sensor and manual

Vad finns i förpackningen

Includes: sensor and manual

Obligatoriska tillbehör

- SC1000 probmodul för 4 givare, 4x 4 - 20 mA UT, relä, 110 - 240 VAC, EU-kabel (Item LXV400.99.2R121)
- SC1000 displaymodul (Item LXV402.99.00001)