



EC Sensor, Hydrogen, PEEK, 50 bar, O-Ring FKM/FPM

Produktnr: 31210.12
SEK Pris: Kontakta oss
Inget leveransdatum anges

Allows you to monitor hydrogen in the power production process.

Hydrogen EC sensor, PEEK, guard ring: platinum, O-ring: FKM/FPM (20 bar)

Specifikationer

Applikation:	Corrosion rate
Certifieringar :	2004/108/EC - EN 61326-1
Flödeshastighet:	Typical Flow Rate
	Membrane 2956A : 50 to 220 mL/min
	Membrane 2952A : 40 to 200 mL/min
	Membrane 2995A : 20 to 70 mL/min
	Membrane 29015A : 20 to 40 mL/min
Garanti :	24 månader
Material:	O-Ring: FKM/FPM
Mätområde:	Range at 25 °C Membrane 2956A : 0 - 75 ppb or 0 Pa - 5 kPa
	Membrane 2952A : 0 - 300 ppb or 0 Pa - 20 kPa
	Membrane 2995A : 0 - 3200 ppb or 0 Pa - 200 kPa
	Membrane 29015A : 0 ppb - 32 ppm or 0 - 2000 kPa
Noggrannhet:	The greater of ±1% of reading, or ±0.09 ppb, or ±6 Pa (Membrane 2952A)
Omgivningstemperatur:	-5 - 100 °C (23 - 212 °F)
Parameter:	Hydrogen
Prov: tryck:	0 - 50 bar
Skyddsklass:	IP68 / NEMA4
Specialfunktioner:	Silver guard ring
Strålning motstånd:	Membrane 2956A : 2×10^4 rad
	Membrane 2952A : 10^8 rad

Membrane 2995A : 10⁸ rad

Membrane 29015A : N/A

Temperaturområde :

Accurate from -5 - 50 °C (23 - 122 °F)

Resistant - temperature from -5 - 100 °C (23 - 212 °F)

Vad ingår i leveransen:

Sensor and manual.

Controller, sensor cable, flow-chamber or process connection must be ordered separately.

Vikt :

140 to 700 grams, depending on the construction materia

Vad finns i förpackningen

Sensor and manual. Controller, sensor cable, flow-chamber or process connection must be ordered separately.