



Filter, TSS glass fiber, pore size 1.5 µm, diameter 110 mm, 100/pk

Produktnr:	2569100
SEK Pris:	Kontakta oss
Skickas inom 2 veckor	

TSS Filters are recommended for use in Standard Methods 2540 C and 2540 D. Optimized surface characteristics of this binderless borosilicate glass microfiber filter eliminates pin-holing and fiber-shedding to ensure consistent, accurate results. Fast flow rate, fine porosity and 1.5 µm particle retention makes the TSS Filter the preferred choice of environmental chemists for total suspended solids analysis of water and wastewater.

Specifikationer

Diameter:	110 mm
Material:	Glass Microfiber
Porstorlek:	1.5 µm
Volym/förpackningsstorlek:	100 /pk