



AS950 Portable Compact Sampler, 12 V, Composite 10 L PE Bottle

Produktnr: ASP.CXXXC121XX
SEK Pris: Kontakta oss
Inget leveransdatum anges

Sampling has never been this easy.

The AS950 Portable Compact Sampler simplifies sampling, turning a once complicated task into an effortless and efficient process. Designed to enhance accuracy and prevent errors, this device ensures reliable results every time, giving operators the confidence that their sampling is being handled precisely.

The AS950 removes the complexity of programming while delivering consistent, reliable data. By simplifying workflows with its user-friendly operation and advanced features like USB data transfer and program copying, it reduces repetitive tasks and enables operators to focus on more critical responsibilities with ease and confidence.

Its real-time error alerts and status updates mean you're always in the loop, so you can address issues quickly and avoid disruptions. Lightweight and highly portable, the AS950 adapts to both field and lab environments, offering dependable support wherever it's needed.

With the AS950, your sampling tasks are no longer a source of stress. Instead, you gain peace of mind, knowing that this equipment is designed to work accurately and efficiently, empowering you to achieve optimal results with ease.

Easiest and most intuitive operation

The large full colour display and intuitive programming give you access to all your programmable criteria on a single screen - eliminating scrolling through menus and supporting error-free operation.

Most convenient data transfer and programming available

The AS950 is the only sampler that utilises a USB drive to upload and download data and copy programs from one sampler to another.

Confidence in your sampling process

The program status screen instantly communicates alarms, missed samples and program progress for quick and easy troubleshooting.

Field convertible for compact or discrete sampling

Weighing only 12.7 kg, the AS950 portable compact sampler is designed for accuracy and convenience. Quickly switch between composite and discrete sampling in the field. Configurable for single or multiple bottle applications, it is specifically designed for use in 18-inch manholes.

Easy maintenance at low cost

Spring-mounted rollers provide long tubing life keeping maintenance costs low. The desiccant and pump tubing can easily be accessed; the replacement is possible without any tools. The rugged see-through pump cover is made for a quick visual inspection.

Specifikationer

Användargränssnittsspråk:	Chinese, English, French, German, Italian, Spanish, Portuguese
Användningsläge :	Continuous or non-continuous
Automatic shutdown:	Multiple Bottle Mode: After complete revolution of distributor arm (unless Continuous Mode is selected)

	Composite Mode: After preset number of samples have been delivered to composite container, from 1 to 999 samples, or upon full container.
Bas Typ:	Compact
Base Configuration:	Portable Compact
Bottle Set:	Composite 2.5 gallon polyethylene bottle kit
Certifieringar :	CE, UL
Data logging :	SAMPLE HISTORY - Stores up to 4000 entries for sample time stamp, bottle number and sample status (success, bottle full, rinse error, user abort, distributor error, pump fault, purge fail, sample timeout, power fail and low main battery).
	MEASUREMENTS - Stores up to 325,000 entries for selected measurement channels in accordance with the selected logging interval.
	EVENTS - Ability to store up to 2000 entries in Sample History logging. Records Power On, Power Fail, Firmware Updated, Pump Fault, Distributor Arm Error, Low Memory Battery, Low Main Battery, User On, User Off, Program Started, Program Resumed, Program Halted, Program Completed, Grab Sample, Tube Change Required, Sensor Communication Errors, Cooling Failed, Heating Failed, Thermal Error Corrected.
Display :	1/4 VGA, Color; self-prompting/menu-driven program
Displaylåsfunktion:	Access code protection prevents tampering
Factory Installed Options:	RAIN/RS485 PORT
	Accepts Hach Rain Gauge (not included) or can be used as RS485 communications
Felsökning:	View event and alarm logs as well as maintenance diagnostics
Garanti :	24 månader
Givare ingår:	Nej
Givares:	None
Givarportar:	None
Husmaterial:	PC/ABS blend, NEMA 4X, 6, IP68, corrosion and ice resistant (Controller)
Ingångar:	One 0/4-20 mA input for flow pacing
Inloppsskölj:	Strainers: Choice of PTFE and 316 stainless steel construction, or all 316 stainless steel in standard size, high velocity, and low profile for shallow depth applications
	Purge: Air purged automatically before and after each sample;
	duration automatically compensates for varying intake line lengths
	Rinse: Intake line automatically rinsed with source liquid prior to each sample, from 1 to 3 rinses
	Retries or Fault: Sample collection cycle automatically repeated from 1 to 3 times if sample not obtained on initial attempt
Internal clock:	±1 second per day at 25 °C
Kommunikationsmöjligheter:	USB and optional RS485 (Modbus)
Lagringsförhållanden:	-30 - 60 °C
Larm:	Configurable alarms that show on status screen and are recorded in diagnostics alarm logs. Alarms can be set for system diagnostics and logging such as program end, sample complete, missed samples and full bottle. Channel alarms are setpoint alarms for the recorded measurements (channels), such as pH, level and power supply voltage.
Ledning:	Vinyl - 25', 3/8" ID x 5/8" OD tubing and PTFE/stainless steel strainer

Manual sampling:	Initiates a sample collection independent of program in progress
Material:	Impact resistant ABS plastic, 3-section construction Double-walled base with 2.54 cm insulation, direct ice contact with bottles (Sampler)
Matningskrav (Spänning):	12 V Battery
Minne:	Sample history: 4000 records; Data log: 325,000 records; Event log: 2000 records
Omgivningstemperatur:	0 - 50 °C
Pausläge:	Battery, 12V Lead acid, 3 pin
Programs:	Dual Programs: Up to 2 sample programs can be run sequentially, in parallel, or according to day of week scheduling; enabling a single sampler to function like multiple samplers
Provbehållare:	1 x 10 L PE
Provintervall:	Selectable in single increments from 1 to 9999 flow pulses or 1 to 9999 mins in one minute increments
Provtagningsläge:	Pacing: Time weighted, Flow weighted, Time table, Flow table, Event Distribution: Single bottle composite, multi-bottle composite, multi-bottle discrete, bottles per sample, samples per bottle or a combination of bottles per sample and samples per bottle
Provtemperatur:	0 - 60 °C
Provvolum:	Programmable in 10 mL increments from 10 - 10,000 mL
Provvolumens noggrannhet:	Typical: ±5% of 200 mL sample volume with: 4.6 m vertical lift, 4.9 m of 3/8" Vinyl intake tube, single bottle, full bottle shut-off at room temperature and 1524 m elevation
Provvolumens repeterbarhet:	Typical: ±5% of 200 mL sample volume with: 4.6 m vertical lift, 4.9 m of 3/8" Vinyl intake tube, single bottle, full bottle shut-off at room temperature and 1524 m elevation
Pump flow rate:	4.8 L/min at 1 m vertical lift with 3/8" intake tube typical
Rain Gauge Input:	Nej
Regnmätare:	Nej
Sample pump:	High-speed peristaltic, dual roller, with 0.95 ID x 1.6 OD cm (3/8" ID x 5/8" OD) pump tube
Sample transport velocity:	0.9 m/s with 4.6 m vertical lift, 4.8 m of 3/8" Vinyl intake tubing, 21 °C and 1524 m elevation
Sample trigger:	When equipped with flow sensor or pH/temperature sensor or peripheral monitoring options, sampling can be triggered upon an upset condition when field selectable limits are exceeded
Språk:	English, French, Spanish, Italian, German, Portuguese, Chinese
Status messages:	Communicates what program is running, if there are any missed samples, when the next sample will be taken, how many samples remain, number of logged channels, time of last measurement, memory available, number of active channels, if alarms were triggered, when alarms were triggered, active sensors and cabinet temperature
Suction Hose Outer Diameter:	1/4" and 3/8" ID PTFE-lined Polyethylene with protective outer cover available in clear and black.
User interface:	Membrane switch keypad with 2 multiple function soft keys
Vad ingår i leveransen:	1 ea. AS950 controller on compact portable base 1 ea. 12 V battery (8754400) 1 ea. Bottle kit (PC010030), includes 1 x 10 L PE bottle w/cap (1918) and full bottle shut-off (8996) 1 ea. 7 m vinyl intake tubing (920) 1 ea. strainer (926)

	(Battery charger 8753500EU sold separately)
Vertical lift:	8.5 m using 8.8 m maximum of 3/8" Vinyl intake tube at sea level at 20 to 25 °C
Vikt :	12.7 kg

Vad finns i förpackningen

1 ea. AS950 controller on compact portable base1 ea. 12 V battery (8754400)1 ea. Bottle kit (PC010030), includes 1 x 10 L PE bottle w/cap (1918) and full bottle shut-off (8996)1 ea. 7 m vinyl intake tubing (920)1 ea. strainer (926)(Battery charger 8753500EU sold separately)