



## AS950 Portable Standard Sampler Bundle, 12 V, 1 x 10 L Bottle, Submerged Area Velocity Sensor, digital pH Sensor

**Produktnr:** ASP.CSXXS12114  
**SEK Pris:** Kontakta oss  
**Inget leveransdatum anges**

### Sampling has never been this easy.

The AS950 Portable Sampler simplifies sampling by providing accuracy and convenience. Weighing only 12.7 kg, it is designed for ease of use and portability. With a large, full-color display, intuitive single-screen programming and USB data transfer capabilities, you can save time and simplify the entire process.

In addition to its easy programming, the AS950 Portable Sampler features an error warning and status screen that eliminates uncertainty and simplifies troubleshooting. You can also save time by copying programs from sampler to sampler, eliminating tedious programming. The sampler is field-configurable for composite or discrete sampling, and maintenance is easy and inexpensive.

If you're looking for the easiest and most intuitive operation, the most convenient data transfer and programming available, and confidence in your sampling process, the AS950 Portable Sampler is the right choice. Simplify your sampling process and order yours today.

#### Easiest and most intuitive operation

The large full colour display and intuitive programming give you access to all your programmable criteria on a single screen - eliminating scrolling through menus and supporting error-free operation.

#### Most convenient data transfer and programming available

The AS950 is the only sampler that utilises a USB drive to upload and download data and copy programs from one sampler to another.

#### Confidence in your sampling process

The program status screen instantly communicates alarms, missed samples and program progress for quick and easy troubleshooting.

#### Field convertible for compact or discrete sampling

Weighing only 12.7 kg, the AS950 portable sampler is designed for accuracy and convenience. Quickly switch between composite and discrete sampling in the field. Configurable for single or multiple bottle applications, it is specifically designed for use in 18-inch manholes.

#### Easy maintenance at low cost

Spring-mounted rollers provide long tubing life keeping maintenance costs low. The desiccant and pump tubing can easily be accessed; the replacement is possible without any tools. The rugged see-through pump cover is made for a quick visual inspection.

---

### Specifikationer

Användargränssnittsspråk:	Chinese, English, French, German, Italian, Spanish, Portuguese
Användningsläge :	Continuous or non-continuous
Automatic shutdown:	Multiple Bottle Mode: After complete revolution of distributor arm (unless Continuous Mode is selected)

	Composite Mode: After preset number of samples have been delivered to composite container, from 1 to 999 samples, or upon full container.
Bas Typ:	Standard
Base Configuration:	Portable Standard
Bottle Set:	Composite 2.5 gallon polyethylene bottle kit
Certifieringar :	CE, UL
Data logging :	SAMPLE HISTORY - Stores up to 4000 entries for sample time stamp, bottle number and sample status (success, bottle full, rinse error, user abort, distributor error, pump fault, purge fail, sample timeout, power fail and low main battery).
	MEASUREMENTS - Stores up to 325,000 entries for selected measurement channels in accordance with the selected logging interval.
	EVENTS - Ability to store up to 2000 entries in Sample History logging. Records Power On, Power Fail, Firmware Updated, Pump Fault, Distributor Arm Error, Low Memory Battery, Low Main Battery, User On, User Off, Program Started, Program Resumed, Program Halted, Program Completed, Grab Sample, Tube Change Required, Sensor Communication Errors, Cooling Failed, Heating Failed, Thermal Error Corrected.
Display :	1/4 VGA, Color; self-prompting/menu-driven program
Displaylåsfunktion:	Access code protection prevents tampering
Factory Installed Options:	RAIN/RS485 PORT
	Accepts Hach Rain Gauge (not included) or can be used as RS485 communications
Felsökning:	View event and alarm logs as well as maintenance diagnostics
Givare ingår:	Submerged Area Velocity and digital pH
Givares:	Non oil-filled 0-10' range, 30' cable with connector; Digital pH sensor for Europe only
Givarportar:	Yes
Husmaterial:	PC/ABS blend, NEMA 4X, 6, IP68, corrosion and ice resistant (Controller)
Ingångar:	One 0/4-20 mA input for flow pacing
Inloppsskölj:	Strainers: Choice of PTFE and 316 stainless steel construction, or all 316 stainless steel in standard size, high velocity, and low profile for shallow depth applications
	Purge: Air purged automatically before and after each sample;
	duration automatically compensates for varying intake line lengths
	Rinse: Intake line automatically rinsed with source liquid prior to each sample, from 1 to 3 rinses
	Retries or Fault: Sample collection cycle automatically repeated from 1 to 3 times if sample not obtained on initial attempt
Internal clock:	±1 second per day at 25 °C
Kommunikationsmöjligheter:	USB and optional RS485 (Modbus)
Larm:	Configurable alarms that show on status screen and are recorded in diagnostics alarm logs. Alarms can be set for system diagnostics and logging such as program end, sample complete, missed samples and full bottle. Channel alarms are setpoint alarms for the recorded measurements (channels), such as pH, level and power supply voltage.
Ledning:	Vinyl - 25', 3/8" ID x 5/8" OD tubing and PTFE/stainless steel strainer
Manual sampling:	Initiates a sample collection independent of program in progress

Material:	Impact resistant ABS plastic, 3-section construction Double-walled base with 2.54 cm insulation, direct ice contact with bottles (Sampler)
Matningskrav (Spänning):	12 V Battery
Minne:	Sample history: 4000 records;
	Data log: 325,000 records;
	Event log: 2000 records
Pausläge:	Battery, 12V Lead acid, 3 pin
Programs:	Dual Programs: Up to 2 sample programs can be run sequentially, in parallel, or according to day of week scheduling; enabling a single sampler to function like multiple samplers
Provbehållare:	1 x 10 L
Provintervall:	Selectable in single increments from 1 to 9999 flow pulses or 1 to 9999 mins in one minute increments
Provtagningsläge:	Pacing: Time weighted, Flow weighted, Time table, Flow table, Event
	Distribution: Single bottle composite, multi-bottle composite, multi-bottle discrete, bottles per sample, samples per bottle or a combination of bottles per sample and samples per bottle
Provvoly:	Programmable in 10 mL increments from 10 - 10,000 mL
Provvolyens noggrannhet:	Typical: ±5% of 200 mL sample volume with: 4.6 m vertical lift, 4.9 m of 3/8" Vinyl intake tube, single bottle, full bottle shut-off at room temperature and 1524 m elevation
Provvolyens repeterbarhet:	Typical: ±5% of 200 mL sample volume with: 4.6 m vertical lift, 4.9 m of 3/8" Vinyl intake tube, single bottle, full bottle shut-off at room temperature and 1524 m elevation
Pump flow rate:	4.8 L/min at 1 m vertical lift with 3/8" intake tube typical
Rain Gauge Enabled:	Ingen
Rain gauge input:	Nej
Sample pump:	High-speed peristaltic, dual roller, with 0.95 ID x 1.6 OD cm (3/8" ID x 5/8" OD) pump tube
Sample transport velocity:	0.9 m/s with 4.6 m vertical lift, 4.8 m of 3/8" Vinyl intake tubing, 21 °C and 1524 m elevation
Sample trigger:	When equipped with flow sensor or pH/temperature sensor or peripheral monitoring options, sampling can be triggered upon an upset condition when field selectable limits are exceeded
Språk:	English, French, Spanish, Italian, German, Portuguese, Chinese
Status messages:	Communicates what program is running, if there are any missed samples, when the next sample will be taken, how many samples remain, number of logged channels, time of last measurement, memory available, number of active channels, if alarms were triggered, when alarms were triggered, active sensors and cabinet temperature
Suction Hose Outer Diameter:	1/4" and 3/8" ID PTFE-lined Polyethylene with protective outer cover available in clear and black.
Temperatur:	Operating: 0 - 49 °C
	Storage: -40 - 60 °C
User interface:	Membrane switch keypad with 2 multiple function soft keys
Vad ingår i leveransen:	1 ea. AS950 controller with sensor ports on standard portable base
	1 ea. 12 V battery (8754400)
	1 ea. Bottle kit (PS010030), includes 1 x 10 L PE bottle w/cap (1918), container support (1502) and full bottle shut-off (8996)
	1 ea. 7 m vinyl intake tubing (920)
	1 ea. strainer (926)
	1 ea. Non oil-filled 0-3 m range submerged area velocity sensor AV9000S with 9 m cable (77065-030EU)

	1 ea. AV9000S interface module (9504600)
	1 ea. AV9000S mounting hardware (9506900)
	1 ea. digital pH sensor (DPD2P1)
	1 ea. pH adapter cable (9501200)
	(Battery charger 8753500EU sold separately)
Vertical lift:	8.5 m using 8.8 m maximum of 3/8" Vinyl intake tube at sea level at 20 to 25 °C
Vikt :	15 kg

---

**Vad finns i förpackningen**

1 ea. AS950 controller with sensor ports on standard portable base1 ea. 12 V battery (8754400)1 ea. Bottle kit (PS010030), includes 1 x 10 L PE bottle w/cap (1918), container support (1502) and full bottle shut-off (8996)1 ea. 7 m vinyl intake tubing (920)1 ea. strainer (926)1 ea. Non oil-filled 0-3 m range submerged area velocity sensor AV9000S with 9 m cable (77065-030EU)1 ea. AV9000S interface module (9504600)1 ea. AV9000S mounting hardware (9506900)1 ea. digital pH sensor (DPD2P1)1 ea. pH adapter cable (9501200)(Battery charger 8753500EU sold separately)