



EZ9130 Heavy-duty Filtration System for digestate samples, pore size 200 µm, 1 stream

Produktnr: EZ9130.XX330091
SEK Pris: Kontakta oss
Tillgänglig

Universal self-cleaning filtration for digestate samples - compatible with the EZ7200 Series

About the EZ9100 Series

The successful implementation of online analysers in process control strategies could not have been achieved without the development of a new generation of automatic sampling and sample preconditioning systems. The EZ9100 Series are the result of many years of field experience in combining analysers with filtration units.

Simplified operation by self-cleaning action

All preconditioning systems are designed for fully automatic operation and require virtually no human intervention. Basically all systems are incorporated either with a blow-back action by instrument air, or a specific cleaning cycle. This fundamental design principle does not merely allow trouble-free sampling, moreover it contributes to high up-times.

The EZ9130 is a filtration system developed specifically for sampling wet type anaerobic digesters to make solid-free samples available for online analysis. Devoid of overly complex engineering, the filtration can handle the difficult properties of sludge and wastewaters charged with high levels of insoluble constituents:

- Self-cleaning sample filtration with various pore sizes
- Large-bore pneumatic ball valves for sample and drain
- Automatic cleaning by solenoid controlled instrument air
- PLC or analyser controlled cleaning frequency

Specifikationer

Antal provströmmar:	1 stream
	Optional:
	1 to 8 streams
Cleaning:	Automatic blowback by solenoid controlled instrument air
Dimension (H x B x D):	1150 mm x 750 mm x 200 mm
Dränering:	Overflow sample D=50 mm; overflow Static Pressure Regulator 3/8" OD

Earth connection:	Dry and clean earth pole with low impedance (< 1 Ohm) using an earth cable of > 2.5 mm ²
Instrument air:	Dry and oil free according to ISA-S7.0.01-1996 quality standard for instrument air
Material:	Filter: SS 316L
	Piping: PVC
	Manual ball valves:PVC
	Tubing: Norprene, PFA, PE
	Panel: weather resistant Trespa
Matningsspänning:	24 VDC, powered by analyser
Porstorlek:	200 µm
Provtemperatur:	Max. 65 °C
Required fast loop:	2 m/s
Rinse water pressure:	3/8" BSPF, 4 bar max.
Size:	200 µm
Skyddsklass:	IP55
Specialfunktioner:	Heavy Duty (Anasense)
Specialkommentarer:	Backflush valve controlled by Analyzer
Vikt :	18 kg