



## Immersion housing IN63, PVC, 0...60 °C, L = 800 mm, automatic sensor cleaning

|                           |                   |
|---------------------------|-------------------|
| <b>Produktnr:</b>         | <b>LZU6301.99</b> |
| SEK Pris:                 | Kontakta oss      |
| Inget leveransdatum anges |                   |

For single 12 mm sensor.

---

### Specifikationer

|                    |             |
|--------------------|-------------|
| Längd:             | 800 mm      |
| Material:          | PVC         |
| Temperaturområde : | 0 - 60 °C   |
| Tryckområde:       | atmospheric |