



Be Right™



Filter, glass fiber, 0.7UM 47mm, pk/100

Produktnr:	2513801
SEK Pris:	Kontakta oss
Skickas inom 2 veckor	

Glass fiber filter ideal for volatile suspended solids of water and wastewater. Also ideal for TCLP analysis. Filters can withstand temperatures of 550°C (1022°F).

Specifikationer

Diameter:	47 mm
Material:	Glass Microfiber
Porstorlek:	0.7 µm
Volym/förpackningsstorlek:	100 /pk