



Enhet för förurning/rengöring av amperometriska sensorer

Produktnr: LZ Y051
SEK Pris: Kontakta oss
Skickas inom 2 veckor

Many amperometric processes have optimal pH ranges in which they will be most accurate and produce the best results. Adding an acidification/cleaning unit onto instruments such as the CL10 sc can help to ensure that samples stay range that is favorable for measurement.

Specifikationer

Depth panel:	107 mm
Flöde:	Min 0.24, max. 1 mL/min
Garanti :	24 månader
Height (panel):	270 mm
Kabellängd:	1 m digital
Material:	Carboy: PEHD (high-density polyethylene)
Matningskrav (Spänning):	12 V DC
Processanslutning:	0.125 " NPT (for tube fittings)
Säkringsklass:	T, 250 mA, 250V
Vad ingår i leveransen:	Förurningsenhet, karbuljong, 1 M digital förlängningskabel, slangats och instruktioner.
Volym:	10 L chemicals not supplied
Width:	250 mm

Vad finns i förpackningen

Förurningsenhet, karbuljong, 1 M digital förlängningskabel, slangats och instruktioner.