



Sanitary Electrodeless Conductivity Sensor, PFA Body Material

Produktnr: 3708E2T
SEK Pris: Kontakta oss
Inget leveransdatum anges

Sensor with sanitary body style, PFA, immersion or flow-through probe works with analogue controller or optional with SC controller by AD 3700 digital gateway.

Wide Measuring Range

Hach's Inductive Conductivity Sensors measure 200 up to 2,000,000 microSiemens/cm. A built-in Pt 1000 RTD compensates the measured conductivity for changes in process temperature.

Low Maintenance Design

The inductive sensor design eliminates polarization and electrode coating problems that commonly affect conventional contacting electrode-type conductivity sensors.

Versatile Mounting Styles

Sensors can be installed using a choice of four mounting styles—immersion, insertion, union, and sanitary.

Principle of Operation

Inductive conductivity sensors induce a low current in a closed loop of solution, then measure the magnitude of this current to determine the solution's conductivity. The conductivity analyzer drives Toroid A, inducing an alternating current in the solution. This current signal flows in a closed loop through the sensor bore and surrounding solution. Toroid B senses the magnitude of the induced current which is proportional to the conductance of the solution. The analyzer processes this signal and displays the corresponding reading.

Withstands Harsh Environments

The inductive sensor is available in sanitary (CIP) flange style and convertible styles in PFA, polypropylene, PEEK, and PVDF material. Select sensors can withstand high pressures and temperatures.

Specifikationer

Body Material:	PFA
Cellkonstant k:	4.44 cm ⁻¹
Flöde:	Rate 3 m (10 ft.) per second, maximum
Fuktade material:	Polypropylene, PVDF, PEEK or PFA
Garanti :	24 månader
Givartyp:	Analog
Kabellängd:	6 m (20 ft)
Längd:	127 mm
Material:	PFA
Mätområde:	200 µS/cm - 2000000 mS/cm

Monteringsform:	Sanitary
Neddopningsdjup:	69.85 mm
Noggrannhet:	0.01 % of reading, all ranges
Omgivningstemperatur:	-10 - 200 °C (Sensor - limited by body material)
Processanslutning:	2 " flange design, suitable for CIP/SIP, with special cap and EPDM compound gasket
Sensor cable:	Polypropylene and PVDF Sensors:
	5 conductor (plus two isolated shields) cable with XLPE (cross-linked polyethylene) jacket; rated to 150 °C (302°F); 6 m (20 ft.) long
Specialkommentarer:	Composition:
	AD 3700 digital gateway 3708E2T analogue inductive conductivity sensor 1 m digital cable
Temperaturgivare:	Temperature Compensator Pt 1000 RTD
Tryckområde:	13.8 bar vid 200 °C
Vad ingår i leveransen:	Includes: sensor with 6 m cable and manual

Vad finns i förpackningen

Includes: sensor with 6 m cable and manual