



Contacting Conductivity Gateway

Produktnr: 6120700.99
SEK Pris: Kontakta oss
Tillgänglig

Digital Gateway is used to operate analog conductivity sensors of all ranges and connect them with a digital controller. Extension cables and the controller must be ordered separately.

Specifikationer

Arbetsluftfuktighet:	0 - 95 % relative humidity, non-condensing
Diameter:	34 mm
Kalibreringsmetod :	Comparison to standard
Kommunikation:	MODBUS
Konduktivitet, noggrannhet:	± 2 % of reading
Lagringsförhållanden:	less than 95% Relative Humidity
Längd:	175 mm
Mätområde:	0.01 - 20 µS/cm if cell constant K=0.01
Omgivningstemperatur:	-20 - 60 °C at 0 - 95% RH (non-condensing)
Repeterbarhet:	± 0.5 % of reading
Responstid T90:	30 s
Temperaturnoggrannhet:	± 0.1 °C
Vad ingår i leveransen:	Includes: gateway, gateway user instructions
Vikt :	0,145 kg

Vad finns i förpackningen

Includes: gateway, gateway user instructions