



2EL conductivity sensor, K=1, Pg13.5, 120 mm, graphite electrode

Produktnr:

LZY082

SEK Pris:

Kontakta oss

Tillgänglig

2-electrode sensor designed for clean water conductivity measurements with in-built temperature element. Installation in flow or immersion fitting. Measuring ranges depending on used controller.

Specifikationer

Cellkonstant k:	1 cm ⁻¹
Diameter:	12 mm
Elektrodmaterial:	UDEl polysulfone (PSU) and epoxy
Garanti :	24 månader
Givargänga:	Pg 13,5
Kabellängd:	5 m fixed and sealed cable
Längd:	120 mm
Mätområde:	1 - 20000 µS/cm SI792 / SI794
Mätprincip:	2-electrode contacting conductivity
Omgivningstemperatur:	-5 - 80 °C
Packning :	EPDM gasket
Temperaturgivare:	Pt1000 integrated
Tryckområde:	0 - 6 bar
Vikt :	0,15 kg