



Polymetron 8311 2-EL conductivity sensor, $K=0.1 \text{ cm}^{-1}$, spare sensor for D3411

Produktnr: 08311=A=0000
SEK Pris: Kontakta oss
Skickas inom 1 vecka

Specifikationer

Cellkonstant k:	0.1 cm^{-1}
Flödeshastighet:	Minimum: 100 mL/min (6 L/h) with homogeneous flow sample or 330 mL/min (20 L/h)
Garanti :	6 månader
Kabelanslutning :	Fiber-glass-reinforced polyester plug head
Kapslingsklass:	IP65
Kärskonstant:	1.00 if mounted in 8318 flow through chamber
Längd:	119.5 mm
Mätområde:	0.1 - 2000 $\mu\text{S}/\text{cm}$
Mätprincip:	2-EL contacting conductivity
Omgivningstemperatur:	125 °C maximum
Processanslutning:	0.75 " NPT thread
Temperaturgivare:	Pt100 Class A
Tryckområde:	Max. 10 bar