



Cable for Polymetron 831x Conductivity Probes, 5 m

Produktnr:	08319=A=0005
SEK Pris:	Kontakta oss
Tillgänglig	

Cable is used to connect the 8310, 8311, 8312, 8315, 8316, and 8317 conductivity sensors to the appropriate controller. Other cable lengths (10 m and 20 m) are available.

Specifikationer

Kabellängd:	5 m
Rating connector:	IP 65
Specialkommentarer:	Plug/cable combination for POLYMETRON 8310, 8311, 8312, 8315, 8316, 8317 sensors