



PVC DN 40 flow chamber, flange-type probe fitting for 8350/8351

Produktnr:	08350=A=9500
SEK Pris:	Kontakta oss
Skickas inom 2 veckor	

Union mount is compatible with all 8350 and 8351 series sensors. Can be used up to 80 °C at 10 bar.

Specifikationer

Diameter:	40 mm
Längd:	98 mm
Material:	PVC
Specialkommentarer:	Tee piece compatible with sensors 8350.3, 8350.4, 8350.5 and 8351