



Analogue combination ORP sensor, 3/4" NPT, 10 m cable

Produktnr: 08351=C=0000
SEK Pris: Kontakta oss
Tillgänglig

Material PPS, Platinum ORP electrode

Specifikationer

Applikation:	ORP for high temps
Drift:	<3 mV/week
Elektrolyt:	Polymer electrolyte, KNO ₃ and KCl
Garanti :	6 månader
Impedans:	Reference impedance @ 25 °C: <50 kΩ Glass impedance @ 25 °C: Platinum
Kabellängd:	10 m
Kontakt:	Fixed cable
Längd:	150 mm
Material:	Reference Electrode: Ag/AgCl
Mätområde:	-1500 mV - 1500 mV
Omgivningstemperatur:	Temperature Maximum: 110 °C (230 °F)
Processanslutning:	0.75 " NPT thread at both ends
Referenselektrod:	None
Slope Range:	N/A
Temperaturgivare:	PT1000
Tryckområde:	Max. 10 bar vid 80 °C
Vikt :	0,62 kg