



## Polymetron 8394 2EL contact cond. sensor, K=0.01cm-1,1.5", sanitary

**Produktnr:** 08394=A=1511  
**SEK Pris:** Kontakta oss  
**Skickas inom 1 vecka**

Analogue 2 electrode conductivity sensor suitable for sanitary applications. Flow-through probe with integrated temperature sensor. Quick disconnect plug for connection to controllers.

---

### Specifikationer

|                       |                                                                                          |
|-----------------------|------------------------------------------------------------------------------------------|
| Cellkonstant k:       | 0.01 cm <sup>-1</sup> ±2 %                                                               |
| Diameter, yttre:      | 18 mm                                                                                    |
| Flödeshastighet:      | Minimum: 100ml/min (6l/hour) with homogeneous flow sample or 330 ml/min (20l/hour)       |
| Fuktade material:     | Glass fiber reinforced polyester,                                                        |
| Kabelanslutning :     | Fiber-glass-reinforced polyester plug head, IP 65                                        |
| Längd:                | 116 mm                                                                                   |
| Material:             | Connector: Glass-fibre reinforced polyester, IP 65                                       |
| Mätområde:            | 0.01 - 20 µS/cm SC controller                                                            |
| Mätprincip:           | 2-EL contacting conductivity                                                             |
| Neddopningsdjup:      | 57.5 mm                                                                                  |
| Omgivningstemperatur: | 150 °C maximum                                                                           |
| Processanslutning:    | 1.5 " Tri-clamp flange                                                                   |
| Specialkommentarer:   | Delivered with test certificate, material conformity certificates, roughness certificate |
| Temperaturgivare:     | Pt100 Class A                                                                            |
| Tryckområde:          | Max. 25 bar                                                                              |