



## Exsickator, icke-vakuum

|                           |                |
|---------------------------|----------------|
| <b>Produktnr:</b>         | <b>1428500</b> |
| SEK Pris:                 | Kontakta oss   |
| Inget leveransdatum anges |                |

Round polycarbonate cover and polypropylene base. Non-Vacuum. Chamber is impervious to alkali and acidic conditions. Recessed rim prevents grease (not included) from contacting bench surfaces when removed and eliminates need for a separate gasket. Dimensions (height x diam): 245 mm x 330 mm (9.7" x 13"). Holds 454 g (1 lb) of dessicant. Ceramic dessicator plate (sold separately) is inert, non-stick, and corrosion resistant. Quadrants crafted into plate for easy tracking of material locations. Plate diameter: 230 mm (9").

---

### Specifikationer

|                            |        |
|----------------------------|--------|
| Volym/förpackningsstorlek: | 1 each |
|----------------------------|--------|